



FLUXO B13

Water Washable Fluorescent Penetrant - BIODEGRADABLE - Level 3

General Appearance & Composition

- Water Washable Fluorescent Penetrant
- Method A/C Type 1 Level 3 according to EN ISO 3452
- Bright and sharp indication with low level of fluorescent background / excellent stability
- FLUXO B13 is a stable solution of biodegradable solvent, nonionic surfactants and fluorescent dyes.
- Processing Temperature: 0° to 50°C
- Associated products:

Cleaner: FLUXO S190 Dry Developer: FLUXO RD1 Solvent Based Developer: FLUXO R175

• Manufacturer: SREM TECHNOLOGIES

Approval & Specifications

- Sensitivity Level 3 according EN ISO 3452
- EN ISO 3452-2
- RCC-M Code
- SAE QPL- AMS 2644 Type 1 Method A/C Level 3
- SAFRAN Pr-5000
- AIRBUS AITM6-1001 Penetrant Inspection
- BOEING BBS7039 Liquid Penetrant Inspection
- ROLLS ROYCE RRP 58003
- AIRBUS Helicopters El070 09-023

- ASME Boiler and Pressure Vessel Code
- ASTM E1417 ASTM E165
- Low in Sulphur & Halogens (< 200ppm)
- ROLLS ROYCE CSS232
- GOODRICH ST2452
- SAFRAN HELICOPTERS ENGINES CCT 00418
- **GE** General Electric Company P3TF2 P3TF47
- LIEBHERR AEROSPACE MFT0253

Properties

- Aspect: Fluorescent Yellow Liquid
- Density (20°C): 0.968
- *Viscosity*: 18 mm²/s (40°C)
- Compatible with any metal & many synthetic materials
- <u>Low viscosity</u>: Biodegradable penetrant with <u>low viscosity</u> (unlike conventional biodegradable penetrants which have a high viscosity). A low viscosity allows little penetrant consumption thanks to a high rate of product recovery during draining.

Flash Point: > 100°C

Health and Safety Advantages

- Free from petroleum distillates / Free from COV / Free from butyl-di-glycol.
- FLUXO B13 is Biodegradable Passes OECD test for ready biodegradability. Biodegradation: > 80 %
- Waste treatment and disposal costs are reduced discharge waste process water directly into the sewage system (depending on local regulation).
- Minimal environmental, occupational health and safety impact.
- NOT FLAMMABLE / NO ODOR / NOT NOCIVE

Instructions for Use

- Cleaning: Remove rust, tinder and all contaminations from the part with FLUXO cleaner
- <u>Application of Penetrant:</u> Apply FLUXO B13: Application by immersion, spraying, brushing, dipping, electrostatic spraying etc... Allow to penetrate for at least 10 minutes.
- Removal: Remove the excess penetrant from the surface under UV Light, with water. If you can't or don't want to use water, remove the excess penetrant with solvent FLUXO S190.
- <u>Drying:</u> Begin drying procedure immediately after water wash.
- Developing: Apply FLUXO developer on the part, achieving a thin and uniform layer.
- <u>Inspection:</u> Parts shall be inspected under UV light as per ISO 3059 standard requirements. Surface defects will appear as fluorescent indication.

Shelf Life

• Minimum of 5 years, stored at room temperature. Please refer to the Safety Data Sheet

Pack Sizes

Drum 1L - 5L - 20L - 60L - 200L - 1000L

SREM TECHNOLOGIES

ZI Ouest - Rue des Frères Chappe - 72200 LA FLECHE - FRANCE - Tél +33 (0) 2.43.48.15.10 - Fax +33(0) 2.43.45.25.26 - www.srem.fr - info@srem.fr



Version: 06/2024